


Habasit Saniclip Retrofit Kit

Enjoy the benefits of the Saniclip with your existing HabasitLINK® belts



From farm to table, the food we eat is the result of many people and industries working together. Amidst this intricate network of production, there is one steadfast priority: food safety.

Enter the Saniclip – a symbol of simplicity that enhances food safety by streamlining belt hygiene. The Saniclip allows line operators to remove and install a belt in seconds without tools.

In the past, the Saniclip had to be ordered alongside the belt. That is no longer the case.


Introducing the Saniclip retrofit kit. The kit provides a simple and effective option to add the Saniclip to your existing Habasit plastic modular belts. This is a tailored kit for your belt, allowing you to enjoy the benefits of the Saniclip rod retention system.

Unlock a world of benefits.

- Comprehensive kit includes extra belt modules and rods
- Plug-and-play no module cutting required
- Available for 19 plastic modular belt styles

Benefits of the Saniclip

- Simplified rod and belt removal; no special training needed.
- Patented, tool-free design allows you to remove the belts quickly with just your hands.
- Enhanced usability in slippery conditions thanks to its textured plug or lever design.
- Avoid the risk of rods or modules breaking during removal or replacement.
- Yellow module can be easily spotted from a distance.



Ordering is easy.

Just follow these steps:

- 1. Measure the width of your belt.
- 2. Take a picture of your belt showing its full width, from one edge to the other.
- 3. Identify your belt style. Please see the table below for compatible belt styles.
- 4. Contact Habasit America Customer Care with this information

Installation is simple.

Scan the QR code to view the installation video.



Pitch mm (in.)	Belt family	Belt style compatibility	System	Module width mm (in.)
8 mm <i>(0.3")</i>	M0870	M0863M0876M0870M0885	Plug	203 mm <i>(8")</i>
12 mm <i>(0.5")</i>	M1065	o M1065	Plug	254 mm <i>(10")</i>
12 mm <i>(0.5")</i>	M1185	o M1185	Plug	127 mm <i>(5")</i>
12 mm <i>(0.5")</i>	SM605	• SM605 • CM650	Plug	51 mm <i>(2")</i>
25mm <i>(1″)</i>	IS610	• IS610 • CT610	Lever	76.2mm <i>(3")</i>
25 mm <i>(1")</i>	M2510	M2510M2514M2511M2516	Lever	50 mm <i>(1.97")</i>
25 mm <i>(1")</i>	M2540	o M2540	Lever	130 mm <i>(5.12")</i>
50 mm <i>(2")</i>	M5060	M5060M5067M5064M5085	Lever	152 mm <i>(6")</i>